



#### **FEATURES**

- Compact TSOP-6 SMT package
- Customized using passive external components
- Protects against both positive- and negative-ESD, in accordance with ESD standards such as:
  - ANSI/ESD STM5.1
  - ➤ MIL-STD 833-c
  - > IEC 61340-2-1
  - ➤ IEC 61000-4-2
- Protects against reverse bias (reverse polarity)
- Lead (Pb)-free component in accordance with RoHS 2002/95/EC and WEEE 2002/96/EC



- Protecting laser diodes from direct and indirect ESD
- Protecting laser diodes from surges during power-up and power-down
- May be used to protect other optoelectronic devices such as Photodiodes and LEDs





#### **GENERAL DESCRIPTION**

The TSOP6/4G-20V is our fourth-generation LASORB Semiconductor Device. It serves as the heart of all of our encapsulated LASORB components, and it is also sold separately for direct integration into OEM devices. When used along with one or two external bias resistors and a single capacitor, its response can be customized to protect virtually any laser diode or series string of laser diodes. The TSOP6/4G-20V Semiconductor Device provides protection against reverse bias as well as fast-changing forward bias conditions.

#### **ORDERING INFORMATION**

The part number provided below is for the standard LASORB TSOP6 Semiconductor Device, operable up to 20V. For other operating voltage levels, contact Pangolin.

Device part number	Comment			
TSOP6/4G-20V	For applications up to 20 volts			


Document Number: TSOP6/4G-9016



## ELECTRICAL CHARACTERISTICS @ T<sub>J</sub> = 25° C

Parameter	Min.	Тур.	Max.	Units	Conditions	
Maximum LDA to LDK Voltage			20	V	leakage current = 30mA	
ESD Event Pulsed Current			50	Α	Absolute Maximum	
20 microsecond Pulsed Current			30	Α	Absolute Maximum	
Continuous Power Dissipation			2	W	25° C	
Junction and Storage Temperature Range	-55		+150	°C	Absolute Maximum	
LDA to LDK impedance when active			0.033	Ω		
LDA to LDK leakage current when inactive			10	uA	LDA to LDK = 15V	
Continuous Reverse Bias Current			2.9	Α	Absolute Maximum	
Reverse Bias Recovery Time		22	29	nS	I = 8A	

### TSOP-6 PIN FUNCTIONS AND MARKING DESCRIPTION



# **Marking notes:**


D4 = Fourth-generation LASORB device


TA12 = Manufacture Lot Number

Document Number: TSOP6/4G-9016




## **TSOP-6 Package Dimensions**





#### RECOMMENDED LAND PATTERN

### **Dimensions in Milimiters and Inches**



<b>Millimeters</b>	Min.	Nom.	Max.	Inches	Min.	Nom.	Max.
Α	0.90		1.25	Α	0.035		0.049
<b>A</b> 1	0.00		0.15	<b>A</b> 1	0.00		0.006
A2	0.70	1.10	1.20	A2	0.028	0.043	0.047
b	0.30	0.40	0.50	b	0.012	0.016	0.020
С	0.08	0.13	0.20	С	0.003	0.005	0.008
D	2.70	2.90	3.10	D	0.106	0.114	0.122
E	2.50	2.80	3.10	E	0.098	0.110	0.122
E1	1.50	1.60	1.70	E1	0.059	0.063	0.067
е	0.95 BSC		е	0.037 BSC			
e1	1.90 BSC		e1	0.075 BSC			
L	0.30		0.60	L	0.012		0.024
Θ1	0°		8°	Θ1	0°		8°

## Notes:

- Package body sizes exclude mold flash and gate burrs. Mold flash at the non-lead sides should be less than 0.1 mm [0.004 inches].
- Dimension L is measured in gauge plane.
- Tolerance =/- 0.1mm [0.004 inches] unless otherwise specified.
- Followed from JEDEC MO-178C & MO-193C.

Controlling dimension is in millimeters, converted inch dimensions are not necessarily exact.

Document Number: TSOP6/4G-9016



#### MORE INFORMATION

More information about LASORB, including additional application hints and tips can be found on the LASORB web site at <a href="https://www.lasorb.com">www.lasorb.com</a>.

## PATENT AND TRADEMARK INFORMATION

Australia Patent Number: 2009268619

German Patent (Utility Model) Number: 20 2009 013 825.9

United States Patent Number: 8,902,557

International Patent Application Number: PCT/US2009/049999

Other International Patents Pending

LASORB is a trademark of Pangolin Laser Systems, Inc.

## U.S. Headquarters:

Pangolin Laser Systems, Inc. 9501 Satellite Boulevard, Suite 109 Orlando, FL 32837 – USA

Phone: +1-407-299-2088 Fax: +1-407-299-6066

## **Central Europe Branch Office:**

Pangolin d.o.o. Podutiška cesta 75 1000 Ljubljana, SLOVENIA Phone: +386-1-517-4270

Fax: +386-1-517-4275

Document Number: TSOP6/4G-9016 www.lasorb.com